




APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/18	



SD-MMNXX-FFBBL-SX0-000
7=IP67



SPECIFICATIONS:

Material:

Housing: PPS, rated UL 94V-0, Color: Black

Contacts: Phosphor Bronze, Gold Flash plated

Plug Shell: Zinc Alloy, Nickel plated

Locking collar: Zinc Alloy, Nickel plated

Spring 1: Stainless Steel

Spring 2: Stainless Steel

O-ring 1: EDPM

Back shell: Zinc Alloy, Nickel plated

Shielding: Phosphor Bronze, Nickel plated

O-ring 2: EDPM

Clamp: Brass, Nickel plated

O-ring 3: NBR, Color: Black

Strain relief collar: Nylon 66, rated UL 94V-0, Color: White

Tightneing collar: PPS, Color: Brown

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES
.X $\pm .10$ $\phi .X$ $\pm .10$
.XX $\pm .020$ $\phi .XX$ $\pm .015$
.XXX $\pm .015$ $\phi .XXX$ $\pm .010$

APPROVALS		DATE
DRAWN	HR	11/23/18
CHECKED	AC	11/23/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
WATERPROOF CONNECTOR, FEMALE DIN,
ASSEMBLY, LOCK TYPE, SOLDER

SIZE	PART NO.	REV.
X	SD-MMNXX-FFBBL-SX0-000	-
REF:	S00298T	SCALE: NTS
SHEET 1 OF 1		