




APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/18	



SD-PNLXX-FFTAL-S00-000



SPECIFICATIONS:

Material:
 Housing: Nylon 46, rated UL 94V-0, Color: Black
 Contacts: Phosphor Bronze, 5u" min. Gold
 Shell A: Zinc Alloy, Nickel plated
 Shell B: Brass, Nickel plated
 O-ring A: NBR, Color: Black
 Screw: Alloy Steel, Nickel plated
 Clamp: Brass
 SR: TPR
 Environmental:
 Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ±.10 .XX ± .020 Ø.XX ±.015 .XXX ± .015 Ø.XXX ±.010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			TITLE		WATERPROOF CONNECTOR, FEMALE M8 DIN, ASSEMBLY, SCREW TYPE, SOLDER	
DRAWN		HR	DATE			
CHECKED		AC	11/23/18			
APPROVED						
			SIZE	PART NO.	REV.	
			X	SD-PNLXX-FFTAL-S00-000	-	
			REF: S00200T		SCALE: NTS	SHEET 1 OF 1