






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/19/17	
A		UPDATE DRAWING	9/5/19	LH/RC



NUT



SPECIFICATIONS:

Material:
 Housing: PBT, rated UL 94V-0, Color: Black
 Contacts: Brass, 10u" Gold plated
 Nut: Brass, Nickel plated
 O-ring: EPDM, Color: Black
 Electrical:
 Voltage: 2~4 PIN: 250 V
 5 PIN: 60 V
 Current rating: 4 A
 Water Proof: IPX7
 Temperature Rating:
 Operating temperature: -40°C to +85°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 ϕ .X ± .10 .XX ± .020 ϕ .XX ± .015 .XXX ± .015 ϕ .XXX ± .010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710
APPROVALS DRAWN HR 5/19/17 CHECKED CK 5/19/17 APPROVED			TITLE WATERPROOF CONNECTOR, FEMALE, M12, A-CODING, SEMI-FINISHED PRODUCT, UNSHIELDED		
SIZE X REF: S00298T			PART NO. SD-PMAXX-FFTS		REV. A
SCALE: NTS			SHEET 1 OF 1		