



APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	8/30/16	
A		UPDATED PIN ASSIGNMENT	6/22/17	HR/CK
B		UPDATED DRAWING	3/8/19	AY/CK
C		UPDATED DRAWING	5/7/19	AY/AC
D		UPDATE SPEC.	7/5/19	LH/RC



SD-PMAXXX-FFTBR-CXX-XFT
7=IP67 A=UL2464

PART NO.	L
SD-PMAXXX-FFTBR-CXX-3FT	36"±1.80" [914.4±45.72mm]
SD-PMAXXX-FFTBR-CXX-6FT	72"±3.60" [1828.8±91.44mm]
SD-PMAXXX-FFTBR-CXX-10FT	120"±6.000" [3048±152.4mm]



CONTACT : BRASS ; GOLD PLATED.
NUT : BRASS ; NICKEL PLATED.
UL2464 CABLE 2PIN~5PIN 24AWG ; 6PIN~8PIN 26AWG(2A 300V)
OVERMOLD : PVC ; COLOR : BLACK
M12 CONN
DESCRIPTION

SPECIFICATIONS:
Electrical:
Current rating: XXA=1.5A, XXB=2A, XXC=5A
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating:
Operating temperature: -25°C to +85°C
Environmental:
Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 Ø.X ±.10 .XX ±.020 Ø.XX ±.015 .XXX ±.015 Ø.XXX ±.010			ADAM TECH INTERCONNECTS		909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
APPROVALS			DATE			TITLE
DRAWN		HR	8/30/16		SIZE	WATERPROOF CONNECTOR, FEMALE, M12 ASSEMBLY CABLE, RIGHT ANGLE
CHECKED		TW	8/30/16		PART NO.	
APPROVED					REV.	D
REF: S00298T			SCALE: NTS		SHEET 1 OF 1	