




APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/23/18	
A		ADDED DRAWING	9/5/19	LH/RC



SD-PNNXX-MMLAL-S00-000



SPECIFICATIONS:

Material:

Housing: Nylon 46, rated UL 94V-0, Color: Black

Contacts: Brass, Gold Flash plated

Shell A: Zinc Alloy, Nickel plated

Shell B: Brass, Nickel plated

Shell C: Brass, Nickel plated

Screw: Alloy Steel, Nickel plated

Clamp: Brass

SR: TPR, Color: Black

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	HR	11/23/18
CHECKED	AC	11/23/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
WATERPROOF CONNECTOR, MALE DIN,
ASSEMBLY, SHELL LOCK TYPE, SOLDER

SIZE	PART NO.	REV.
X	SD-PNNXX-MMLAL-S00-000	A
REF:	S00298T	SCALE: NTS
SHEET 1 OF 2		

6

5

4

3

2


1

APPROVED: _____


DATE: _____ TITLE: _____

Rev AWO # Description Date Appr


SEE SHT 1 OF 2 FOR REVISION




HOUSING + CONTACT + SHELL A




SHELL B




SHELL C



SCREW



CRAMP



SR

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES.X ± .10 Ø.X ± .10
.XX ± .020 Ø.XX ± .015
.XXX ± .015 Ø.XXX ± .010

APPROVALS

DATE

DRAWN

HR

11/23/18

CHECKED

AC

11/23/18

APPROVED

ADAM
TECH
INTERCONNECTS909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE
WATERPROOF CONNECTOR, MALE DIN,
ASSEMBLY, SHELL LOCK TYPE, SOLDER

SIZE

X

PART NO.

SD-PNNXX-MMLAL-SX0-000

REV.

A

REF: S00298T

SCALE: NTS

SHEET 2 OF 2

6

5

4

3

2

1