

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev

AWO #

Description

Date

Appr

-

RELEASED

11/23/18

D

D

C


C

B

B


A

A




HOUSING + CONTACT + SHELL A

SHELL B + SHELL C + SPRING




SD-PNNXX-FFLAL-S00-000




04



05



06



07

06A (Small Crimp)

SPECIFICATIONS:

Material:

Housing: Nylon 46, rated UL 94V-0, Color: Black

Contacts: Brass, Gold Flash plated

Shell A: Zinc Alloy, Nickel plated

Shell B: Brass, Stain Nickel plated

Shell C: Brass, Nickel plated

Spring: Stainless Steel, Nickel plated

Screw: Alloy Steel, Nickel plated

Clamp: Brass

SR: NBR, Color: Black

Environmental:

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS

DATE

DRAWN

HR

11/23/18

CHECKED

AC

11/23/18

APPROVED

ADAM
TECH
INTERCONNECTS909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE
WATERPROOF CONNECTOR, FEMALE DIN,
ASSEMBLY, SHELL LOCK TYPE, SOLDER

SIZE

X

PART NO.

SD-PNNXX-FFLAL-S00-000

REV.

-

REF: S00200T

SCALE: NTS

SHEET 1 OF 1

6

5

4

3

2

1