






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	03/06/13	
A		REVISED DIM. & SPEC.	7/10/14	AY/SY
B		UPDATE DIM.	2/2/16	AY/WY
C		UPDATE DRAWING	9/18/17	HR/IC



SPECIFICATIONS:




Material:
 Top cage: Copper Alloy
 Bottom cage: Copper Alloy
 Temperature Rating:
 Operating temperature: -40°C to +85°C
 Storage temperature: -55°C to +105°C
 Environmental:
 Lead free, RoHS compliant




UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS DRAWN TW CHECKED AH APPROVED			DATE 03/06/13 03/06/13		
TITLE SMALL FORM FACTOR CAGE, 1PORT, DIP TYPE SOLDER TAILS			SIZE X	PART NO. SFC-1-ST	REV. C
REF: S00005C			SCALE: NTS	SHEET 1 OF 2	

APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
SEE SHT 1 OF 2 FOR REVISION				



DETAIL A



B6B LAYOUT (TOP VIEW)
PCB THICKNESS=3.0mm
B TOLFRANCFS+/-

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES			ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
.X	± .10	Ø.X	±.10	TITLE SMALL FORM FACTOR CAGE, 1PORT, DIP TYPE SOLDER TAILS	
.XX	± .020	Ø.XX	±.015		
.XXX	± .015	Ø.XXX	±.010		
APPROVALS		DATE		SIZE X	
DRAWN	TW	03/06/13			
CHECKED	AH	03/06/13		PART NO. SFC-1-ST	
APPROVED				REF: S00005C	SCALE: NTS
				SHEET 2 OF 2	