





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/2/21	



PANEL CUTOUT
 MAX. PANEL THICKNESS
 4 mm



SW-PB7-01PB4EBRXM

Button	Color
R	Red
G	Green
Y	Yellow
B	Blue
W	White
BK	Black

SPECIFICATIONS:

Material:
 Bushing: Zinc Alloy, Nickel plated, color: Black
 Base: PA

Contact: Silver alloy, (2.0x0.5mm)

Button: PBT

Electrical:

Switch Rating: 2A @ 36V DC

Contact resistance: 50 mΩ max initial.

Insulation resistance: 1000M ohms min.

Dielectric withstanding voltage: 1,500 VAC

Electrical Life: 200,000 cycles min.

Mechanical:

Operating Force: 3.5N

Nut Torque: 0.3Nm max.

Temperature Rating:

Operating temperature: -25°C to +55°C

Environmental:

IP65 Front Panel Protection

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
 ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

DRAWN	WX	11/2/21
CHECKED	RC	11/2/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
 AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
 PERMISSION FROM ADAM TECH

**ADAM
 TECH**

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE
 SWITCH, ANTI-VANDAL, PUSH BUTTON, SPST,
 OFF-MOM, 12mm, RAISED COLOR BUTTON

SIZE X	PART NO. SW-PB7-01PB4EBRXM	REV. -
-----------	-------------------------------	-----------

REF: S00198T	SCALE: NTS	SHEET 1 OF 1
--------------	------------	--------------