




APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/2/21	
A		UPDATE SPEC.	11/12/21	WX/RC

D

D



C

C

## SPECIFICATIONS:

Material:

Body: PA, Rated UL94V-0

Bushing: Stainless Steel, Varnish polished

Button: Stainless Steel, Varnish polished

Contact Material: Silver Alloy, (2.8X0.5mm)

Nut: Brass, Nickel plated

## Electrical:

Voltage rating: 250V

Current rating: 5A max

Contact resistance: 50 mΩ max.

Insulation resistance: 1000M ohms min @ 500V DC.

Dielectric withstanding voltage: 2000V RMS, 50Hz.

Electrical Life: 50,000 cycles min at full load.

## Mechanical:

Torque: 0.6Nm max.


Temperature Rating:

Operating temperature: -25°C to +55°C

## Environmental:

Sealed IP65 Rated

Lead free, RoHS compliant



SW-PB7-03LB5CFRXXXXX

"x"	LED Color
R	Red
G	Green
Y	Yellow
O	Orange
B	Blue
W	White

LED Voltage	
2.8V	2.8V AC/DC
6V	6V AC/DC
12V	12V AC/DC
24V	24V AC/DC
110V	110V AC/DC
220V	220V AC/DC

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS  
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	ØX ± .10
.XX ± .020	ØXX ± .015
.XXX ± .015	ØXXX ± .010

DRAWN JJ 11/2/21

CHECKED RC 11/2/21

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY  
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN  
PERMISSION FROM ADAM TECH

**ADAM TECH**

TITLE: SWITCH, ANTI-VANDAL, PUSH BUTTON,  
25mm, LIGHTED RING, SPDT, LATCHING, N.O.-N.C.

SIZE X PART NO. SW-PB7-03LB5CFRXXXXX REV. A

REF: S00198T SCALE: NTS SHEET 1 OF 1