





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/20/21	
A		UPDATE SPEC.	6/21/21	WX/RC



RECOMMENDED PCB LAYOUT



CIRCUIT DIAGRAM
(SPDT) ON-MOMENTARY

SPECIFICATIONS:

Material:

Movable Contact: Copper Alloy, Silver Plated

Terminal: Copper Alloy, Silver Plated with outer layer in gold plating

Electrical:

Voltage rating: 120VAC or 38VDC

Current rating: 1 Amps

Contact resistance: 10 m Ω max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,000V RMS @Sea level

Mechanical:

Waterproof: IP68

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLES
 .X $\pm .10$ $\phi .X$ $\pm .10$
 .XX $\pm .020$ $\phi .XX$ $\pm .015$
 .XXX $\pm .015$ $\phi .XXX$ $\pm .010$

APPROVALS		DATE
DRAWN	WX	2/20/21
CHECKED	AC	2/20/21
APPROVED		

ADAM
TECH

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE
 PUSHBUTTON SWITCH, VERTICAL, ON-MOMENTARY
 SPDT, GOLD OVER SILVER PLATED, PCB TYPE, IP68

SIZE X	PART NO. SW-PB8-AA00B11GE-2	REV. -
REF: S00198T	SCALE: NTS	SHEET 1 OF 1