




APPROVED: \_\_\_\_\_

DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/4/21	


D




C



HEX NUT





LOCK WASHER



ANTI ROTATIONAL WASHER

## INCLUDED HARDWARE

CIRCUIT DIAGRAM  
(SPDT) ON-ON

## SPECIFICATIONS:

## Material:

Movable Contact: Copper Alloy, Silver Plated

Terminal: Copper Alloy, Silver Plated

## Electrical:

## Rating:

6 Amps with resistive load @ 125VAC or 28VDC

3 Amps with resistive load @ 250VAC

Contact resistance: 10 mΩ max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500V RMS @Sea level

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED  
ALL DIMENSIONS ARE INCHES [MM]  
TOLERANCES: EXCEPT AS NOTED  
INCHES HOLES  
.X ± .10 ØX ± .10  
.XX ± .020 ØXX ± .015  
.XXX ± .015 ØXXX ± .010

APPROVALS		DATE
DRAWN	WX	3/4/21
CHECKED	AC	3/4/21
APPROVED		
SIZE	PART NO.	REV.
X	SW-PB8-AA22A1QE-3	-
REF:	S00198T	SCALE: NTS
		SHEET 1 OF 1

**ADAM**  
**TECH**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE  
PUSHBUTTON SWITCH, ON-ON, SPDT  
COPPER ALLOY SILVER PLATED, SOLDER TYPE