






APPROVED: _____
DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	1/26/21	



HEX NUT





LOCK WASHER



ANTI ROTATIONAL
WASHER

INCLUDED HARDWARE



CIRCUIT DIAGRAM
(SPDT) MOMENTARY

SPECIFICATIONS:

Material:

Movable Contact: Copper Alloy, Silver Plated

Terminal: Copper Alloy, Silver Plated

Electrical:

Voltage rating: 120VAC or 38VDC

Current rating: 1 Amps

Contact resistance: 10 mΩ max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500V RMS @Sea level

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE	
DRAWN	LH	1/26/21	
CHECKED	AC	1/26/21	
APPROVED			

TITLE		SNAP-ACTING PUSHBUTTON SWITCH, SPDT, ON-MOMENTARY, SILVER PLATED, SOLDER TYPE	
SIZE	PART NO.	REV.	
X	SW-PB8-AB00A1QE-1	-	
REF:	S00198T	SCALE:	NTS
SHEET 1 OF 1			

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710