





APPROVED: _____

DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	8/10/21	
A		UPDATE SPEC.	10/20/21	WX/RC
B		UPDATED DIM.	6/15/22	JJ/MC
C		UPDATED DIM.	7/25/23	LH/LL1




RECOMMENDED
PANEL CUT-OUT



2 WAY





CIRCUIT DIAGRAM
(3PDT) ON-ON



3 WAY

SW-T1-6X-D-C1-K3
B=ON-ON
E=ON-OFF-ON



SPECIFICATIONS:

Material:

Body: Bakelite, Color: Red Brown

Lever: Brass, Nickel plated

Terminal: Brass, Silver plated

Electrical:

Rating: 15A @ 250V AC

20A @ 125V AC

Contact resistance: 100 mΩ max

Insulation resistance: 100 MΩ min

Dielectric withstanding voltage: 1500V AC/5S

Electrical Life: 10,000 cycles

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ±.10	Ø.X ±.10
.XX ±.020	Ø.XX ±.015
.XXX ±.015	Ø.XXX ±.010

DRAWN	WX	8/10/21
CHECKED	RC	8/10/21
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
SWITCH, TOGGLE MEDIUM, 3PDT,
ON-ON (ON-OFF-ON), SCREW LUG

SIZE X	PART NO. SW-T1-6X-D-C1-K3	REV. C
REF: S00206C	SCALE: NTS	SHEET 1 OF 1