




APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/16/20	
A		UPDATE SPEC.	12/10/25	LW1/LZ

RECOMMENDED
PANEL CUT-OUT

CIRCUIT DIAGRAM
(SPST)

SW-T2-1X-A-A2-M1
A=ON-OFF
C=OFF-(ON)

SPECIFICATIONS:

Material:

Body: Bakelite, Color: Red

Lever: Brass, Nickel plated

Terminal: Brass, Silver plated

Electrical:

Rating: 3A @ 250V AC

6A @ 125V AC

A Contact resistance: 20 mΩ max

Insulation resistance: 1000 MΩ min (500VDC)

Dielectric withstanding voltage: 1500V AC for 1 minute

Electrical Life: 6,000 cycles

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	$\pm .10$	$\emptyset X$	$\pm .10$
.XX	$\pm .020$	$\emptyset XX$	$\pm .015$
.XXX	$\pm .015$	$\emptyset XXX$	$\pm .010$

DRAWN 0W 11/16/20

CHECKED AC 11/16/20

APPROVED

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
adam-tech.com

TITLE
SWITCH, TOGGLE MINIATURE, SPST,
ON-OFF, OFF-(ON), SOLDER TYPE

SIZE	PART NO.	REV.
X	SW-T2-1X-A-A2-M1	A
REF: S00204C	SCALE: NTS	SHEET 1 OF 1