


APPROVED: \_\_\_\_\_  
DATE: \_\_\_\_\_ TITLE: \_\_\_\_\_

Rev	AWO #	Description	Date	Appr
-		RELEASED	12/24/20	
A		UPDATE DRAWING	6/25/21	JJ/RC



SPECIFICATIONS:

Material:

Movable contact: Copper Alloy, Silver plated

Terminals: Brass, Tin plated

Electrical:

Rating: 12A @ 250VAC/125VAC

1/2 HP 125VAC/ 1HP 250VAC/5A 125VAC

Contact resistance: 20 mohms max initial

Insulation resistance: 100 Mohms min @ 500 VDC

Dielectric withstanding voltage: 1500V RMS @ sea level

Electrical life: 30,000 make and break cycles at full load

Temperature Rating:

Operating temperature: -30°C to +85°C

Environmental:

IP68 Protection Class

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS  
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	XX	HOLES
X $\pm .10$	$\varnothing X$ $\pm .10$	
XX $\pm .020$	$\varnothing XX$ $\pm .015$	
XXX $\pm .015$	$\varnothing XXX$ $\pm .010$	

DRAWN OW 12/24/20

CHECKED AC 12/24/20

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY  
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN  
PERMISSION FROM ADAM TECH

**ADAM  
TECH**

909 Rahway Avenue,  
Union, NJ 07083  
Phone: 908-687-5000  
Fax: 908-687-5710

TITLE  
POWER TOGGLE SWITCH, SPDT,  
ON-ON, QC .250 [6.35MM]

SIZE	PART NO.	REV.
X	SW-T4-2B-E-TA1-01	A
REF: S00198T	SCALE: NTS	SHEET 1 OF 1