




Rev	AWO #	Description	Date	Appr
-		RELEASED	11/12/07	
A		REDRAWN	6/27/14	HR/JAC
B		ADDED SHAPE	8/8/14	AV/YC

APPROVED: _____
DATE: _____ TITLE: _____



Positions: 2 thru 28
A = .433 [11.00] x No. of Positions + .098 [2.50]
B = .433 [11.00] x No. of Spaces

SPECIFICATIONS:
Material: PA66, rated UL 94V-0
Insulator color: Black
Contacts: Barss
Screw: M4.0, Steel, Nickel plated
Plating: Tin over Copper underplate overall
Electrical:
Operation voltage: 300 VAC
Current rating: 30 Amps
Mechanical:
Wire Range: 22-12 Awg
Screw Torque Value: 16.0 kg-cm
Dielectric withstanding voltage: 2000 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS Compliant



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
.X	± .10	ØX	± .10	TITLE: .433 [11.00] CENTERLINE BARRIER BLOCK STRAIGHT, BARRIER ENDS, PCB, IRON HARDWARE			
.XX	± .020	ØXXX	± .015				
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN				SS			
CHECKED				11/12/07			
APPROVED				X			
REF: S00046C				TBN-XX-01-B			
SCALE: NTS				REV. B			
SHEET 1 OF 1							