




Rev	AWO #	Description	Date	Appr
-	11457	RELEASED	6/29/11	

APPROVED: _____

DATE: _____ TITLE: _____



SPECIFICATIONS:

Material: Nylon66, rated UL 94V-0
Insulator color: Black
Contacts: Brass, Tin plated
Screws: Steel, Nickel plated
Electrical:
Operating voltage: 300 VAC max.
Current rating: 30 Amps max.
Insulation resistance: 1000 Mohms min. @ DC 500V
Insulation withstands voltage: 2,000 VAC for 1 minute
Mechanical:
Wire range: 22 - 14 AWG
Temperature Rating:
Operating temperature: -40°C to +120°C
Environmental:
Lead free, RoHS compliant

Poles: 2 thru 29
A = .433 [11.00] x No. of Poles + .945 [24.00]
B = .433 [11.00] x No. of Poles + .433 [11.00]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED				INCHES			
.X	± .10	ØX	± .10	.XX	± .020	ØXX	± .015
.XXX	± .015	ØXXX	± .010				
APPROVALS				DATE			
DRAWN				DY			
CHECKED				6/29/11			
APPROVED							
TITLE				BARRIER STRIP, .433" [11.00] PITCH			
STRAIGHT, PCB THRU HOLE							
SIZE				PART NO.			
X				TBN-XX-01-M			
REF: S00031T				SCALE: NTS			
SHEET 1 OF 1							

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710