






APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	



RECOMMENDED MOUNTING CUT-OUT



Poles: 01 thru 15

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Contacts: Copper Alloy, Tin plated

Screw: M4 Steel, Nickel plated

Electrical:

Voltage rating: 600 V

Current rating: 50 A

Contact resistance: 20 mohms

Insulation resistance: 1000 Mohms / DC500V

Dielectric withstanding voltage: 2,500 VAC for 1 minute

Mechanical:

Wire Range: 22~8 AWG

Torque: 1.2Nm/10.6lb.in/12.2Kgf.cm

Temperature Rating:

-40°C to +130°C

Environmental:

Lead free, RoHS compliant.



linear dimension (Tolerances Standard)								—	∕	⊥
variable	to	over	over	over	over	over	over		over	over
range	6	6 to 10	10 to 30	30 to 60	60 to 100	100 to 160	160 to	to 10	to 100	to 100
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE MILLIMETERS
TOLERANCES: EXCEPT AS NOTED

SEE CHART

APPROVALS		DATE
DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

ADAM
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
TERMINAL BLOCK, .512 [13.00] PITCH			
SIZE	PART NO.	REV.	
X	TBU-XX-W2	-	
REF:	S00067C	SCALE:	SHEET 1 OF 1