





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/28/16	
A		UPDATE SPEC.	11/2/20	LH/TW



SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Black

Contacts: Brass, Tin Plated

Screws: M6, Steel, Nickel Plated 

Electrical:

Voltage rating: 600 V

Current rating: 65 A

Dielectric withstanding voltage: 3,000 VAC for 1 minute

Mechanical:

Wire Range: 14~6 AWG

Torque: 2.35 Nm (21.0 Lb-in) 

Temperature Rating:

-40°C to +105°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 12

A = .630 [16.00] x No. of Positions + 1.394 [35.40]

B = .630 [16.00] x No. of Space

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	HR	6/28/16
CHECKED	IC	6/28/16
APPROVED		

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE			
.630 [16.00] CENTERLINE BARRIER BLOCK, VERTICAL PCB TAIL, MOUNT END, W/ CLEAR COVER			
SIZE	PART NO.	REV.	
X	TDJ-XX-01-M-CC	A	
REF: S00046C		SCALE: NTS	SHEET 1 OF 1