





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	1/23/14	
A		REDRAWN	4/9/14	AV/LW



SPECIFICATIONS:
Material: PBT, rated UL 94V-0
Insulator color: White
Contacts: Copper Alloy
Shell: Copper Alloy, Nickel plated
Back Shell: SPCC, Nickel plated
Plating: Tin over Copper underplate on tails.
Gold flash over Nickel underplate on contact area.
Electrical:
Current rating: 1.5A max
Contact resistance: 30 mohms max
Insulation resistance: 1,000 Mohms min
Dielectric withstanding voltage: 500 VAC Max.
Environmental:
Lead free, RoHS compliant



ADAM TECH

909 Railway Avenue, Union, NJ 07083
Phone: 908-687-5000 Fax: 908-687-5710

TITLE: USB, TYPE A, RIGHT ANGLE UPRIGHT THRU-HOLE, SELECTIVE GOLD

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				Holes			
.X	± .10	Ø.X	± .10	.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015	.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010	.XXX	± .015	Ø.XXX	± .010
APPROVALS				DATE			
DRAWN	AY	1/23/14		CHECKED	EH	1/23/14	
APPROVED							
SIZE				PART NO.			
X				USB-A-S-RU-S4			
REF: S00097C				SCALE: NTS			
				SHEET 1 OF 1			