







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	2/7/07	
A		UPDATED DRAWING	12/13/17	HR/YC



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:

Material:

Insulator: Hi-Temp Thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Shell: Brass, Nickel plated

Plating:

Gold Flash over Nickel underplate on contact area

Electrical:

Voltage rating: 30 V

Current rating: 1.5 Amp @ 250 VAC

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 500 VAC

Temperature Rating:

-20°C to +85°C

Environmental:

Lead free, RoHS compliant



UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED
INCHES HOLES

.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS

DATE

DRAWN	SS	2/7/07
-------	----	--------

CHECKED		
---------	--	--

APPROVED		
----------	--	--

ADAME
TECH
INTERCONNECTS

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
USB, TYPE B, SINGLE PORT, RIGHT ANGLE,
THRU-HOLE, GOLD FLASH, HI-TEMP

SIZE X	PART NO. USB-B-S-RA-HT	REV. A
-----------	---------------------------	-----------

REF: S00005C	SCALE: NTS	SHEET 1 OF 1
--------------	------------	--------------