





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/15	
A		ADDED SPEC.	12/18/18	AY/IW



SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Phosphor Bronze

Shield: Brass, Nickel plated

Contact Plating:

Gold Flash over Nickel underplate on contact area,

Tin over Nickel underplate on SMT tails

Electrical:

Rated Voltage And Current: 1.5 A @ 250 VAC min

Contact resistance: 30 mohms max

Insulation resistance: 1,000 Mohms min @ 500 VDC

Dielectric withstanding voltage: 750 VAC for 1 minute

Temperature Rating:

Operating temperature: -55°C to +85°C

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED <table><tr><th colspan="2">INCHES</th><th colspan="2">HOLES</th></tr><tr><td>.X</td><td>± .10</td><td>Ø.X</td><td>±.10</td></tr><tr><td>.XX</td><td>± .020</td><td>Ø.XX</td><td>± .015</td></tr><tr><td>.XXX</td><td>± .015</td><td>Ø.XXX</td><td>± .010</td></tr></table>			INCHES		HOLES		.X	± .10	Ø.X	±.10	.XX	± .020	Ø.XX	± .015	.XXX	± .015	Ø.XXX	± .010	ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710																
INCHES		HOLES																																	
.X	± .10	Ø.X	±.10																																
.XX	± .020	Ø.XX	± .015																																
.XXX	± .015	Ø.XXX	± .010																																
<table><tr><td colspan="2">APPROVALS</td><td>DATE</td></tr><tr><td>DRAWN</td><td>HR</td><td>3/19/15</td></tr><tr><td>CHECKED</td><td>NP</td><td>3/19/15</td></tr><tr><td>APPROVED</td><td></td><td></td></tr></table>			APPROVALS		DATE	DRAWN	HR	3/19/15	CHECKED	NP	3/19/15	APPROVED			<table><tr><td colspan="3">TITLE</td></tr><tr><td colspan="3">UNIVERSAL SERIAL BUS SINGLE PORT, RIGHT ANGLE, SMT</td></tr><tr><td>SIZE</td><td>PART NO.</td><td>REV</td></tr><tr><td>X</td><td>USB-B-S-RA-TSMT-CS1</td><td>A</td></tr><tr><td>REF:</td><td>S00095T</td><td>SCALE: NTS</td></tr><tr><td colspan="2"></td><td>SHEET 1 OF 1</td></tr></table>			TITLE			UNIVERSAL SERIAL BUS SINGLE PORT, RIGHT ANGLE, SMT			SIZE	PART NO.	REV	X	USB-B-S-RA-TSMT-CS1	A	REF:	S00095T	SCALE: NTS			SHEET 1 OF 1
APPROVALS		DATE																																	
DRAWN	HR	3/19/15																																	
CHECKED	NP	3/19/15																																	
APPROVED																																			
TITLE																																			
UNIVERSAL SERIAL BUS SINGLE PORT, RIGHT ANGLE, SMT																																			
SIZE	PART NO.	REV																																	
X	USB-B-S-RA-TSMT-CS1	A																																	
REF:	S00095T	SCALE: NTS																																	
		SHEET 1 OF 1																																	