






APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
08		Modifier Dimension	3/27/14	Eric
09		REDRAWN	3/28/14	HR/TW
10		REDRAWN	3/28/14	HR/TW
-		UPDATE DRAWING	12/19/19	OW/IW



Section A-A

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass, T=0.20MM

Shell: Spcc, T=0.30MM, Nickel plated

Plating:

Gold Flash over Nickel underplate on contact area,

Tin over Copper underplate on solder tails

Electrical:

Contact resistance: 30 mohms max.

Insulation resistance: 1000 Mohms min.

Dielectric withstanding voltage: 500 VAC for 1 minute

Environmental:

Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ± .10 Ø.X ± .10 .XX ± .020 Ø.XX ± .015 .XXX ± .015 Ø.XXX ± .010			ADAM TECH INTERCONNECTS 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS		DATE	TITLE USB CONNECTOR, B TYPE PLUG, SMT, RIGHT ANGLE, SEL-GOLD PLATED		
DRAWN	Eric	11/26/13			
CHECKED	Eric	11/26/13			
APPROVED					
SIZE X		PART NO. USB-BP-S-RA-SMT		REV. -	
REF: S00113C		SCALE: NTS		SHEET 1 OF 1	