

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/28/21	

D





D

C

C

B

B



SPECIFICATIONS:

Material:

Cage: Copper Alloy

Electrometric Gasket: Conductive Rubber

Cage Rear EMI Gasket: Conductive Foam

Front Flange: Zinc Alloy, Tin over Nickel and Copper flash

Front EMI Gasket: Copper Alloy, Matte Tin over Nickel underplate overall

Heat Sink Clip: Copper Alloy

Heat Sink: Aluminum, Anodic Oxidation

Temperature Rating:

Operating temperature: -40°C to +85°C

Environmental:

Lead free, RoHS compliant

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

mm	Angles
.X	± .25
.XX	± .13
.XXX	± .10

DRAWN WX 5/28/21

CHECKED RC 5/28/21

APPROVED

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH
ADAM
TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710TITLE
10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT
DIP TYPE, EMI CLIP W/ GASKET, W/ HEAT SINK

SIZE	PART NO.	REV.
X	XFC-1-CS4-EMI-HSK	-
REF: S00005C	SCALE: NTS	SHEET 1 OF 2

6

5

4

3

2

1

Rev

AWO #

Description

Date

Appr

APPROVED: _____

DATE: _____ TITLE: _____

SEE SHT 1 OF 2 FOR REVISION

D

D

C


C

B

B

A

A



UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE MILLIMETERS. TOLERANCES: EXCEPT AS NOTED

mm	Angles
.X	± .25
.XX	± .13
.XXX	± .10

DRAWN WX 5/28/21

CHECKED RC 5/28/21

APPROVED

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE
10 GIGABIT SMALL FORM FACTOR CAGE, 1PORT
DIP TYPE, EMI CLIP W/ GASKET, W/ HEAT SINK

SIZE	PART NO.	REV.
X	XFC-1-CS4-EMI-HSK	-
REF: S00005C	SCALE: NTS	SHEET 2 OF 2

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

6

5

4

3

2

1