



Representative Image

Alternate Catalog No. SU203M-K50
Catalog No. 2CDS273337R0577

Description: UL489 MCB 3P K 50A 240

UPC No 4016779930451

Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs

SU203M-K50 Miniature Circuit Breaker K-Char., 10kA, 50A, 3P UL489

Descriptors

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

Specifications

Number of Poles	3
Tripping Characteristic	K
Rated Current	50 A
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Product Main Type	SU200M
Rated Voltage (V)	(240 V AC) (96 V DC)
Interrupting Rating acc. to UL489	(240 V AC) 10 kA (96 V DC) 10 kA
Rated Ultimate Short-Circuit Breaking Capacity	(400 V AC) 15 kA
Power Loss	13,5 W at Rated Operating Conditions per Pole 4,5 W