



Representative Image

Alternate Catalog No. F202A-100/0.03110V**Catalog No. 2CSF202199R1100****Description: F202 100A 30mA 110V****UPC No 8012542342939****Home > Modular DIN Rail Products > Residual current devices**

The RCCBs F200 series assures protection against the effects of sinusoidal alternating and direct pulsating earth fault currents, protection, against indirect contacts and additional protection against direct (with sensitivity = 30 mA) contacts. Applications: residential, commercial, industrial. This particular series has the minimum operating voltage of test button of 110V and it is suitable for application at 230V.

Descriptors

Category

Residual current devices

Specifications

Number of Poles	2
Product Main Type	F200
Rated Current	100 A
Rated Operational Voltage	277 V AC
Rated Residual Current	30 mA
Standards	IEC 61008 UL 1053
Type of Residual Current	A type

by ABB