



Representative Image

Catalog No. 035-72775-25

Description: 1-1/2IN STR LT CORD CONN .812-1.000

UPC No 786210069043

Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors

1-1/2 Inch Straight Die Cast Zinc Liquidtight Strain Relief Cord Connector, Cord Range 0.812 to 1.000

Descriptors

Category	Liquid tight connectors
Special Features	Throat Inner Diameter is Nylon Coated for Ease of Wire Pull
Application	Provide Means for Passing a Cord Cable, Armored or Unarmored, Into an Enclosure, Through a Bulkhead or Into a Rigid Conduit

Specifications

Material	Zinc Die Cast
----------	---------------

Classifications

Brand Name	T&B Liquidtight Fittings
------------	--------------------------

Dimensions

Size	1-1/2 Inch
------	------------

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	None
Material housing	Zinc die-cast

by ABB