



Representative Image

## Catalog No. 035-72775-2

**Description:** 1/2IN STR LT CORD CONN .250-.375

**UPC No 786210868905**

**Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors**

1/2 Inch Straight Die Cast Zinc Liquidtight Strain Relief Cord Connector, Cord Range 0.250 to 0.375

### Descriptors

Category	Liquid tight connectors
Special Features	Throat Inner Diameter is Nylon Coated for Ease of Wire Pull
Application	Provide Means for Passing a Cord Cable, Armored or Unarmored, Into an Enclosure, Through a Bulkhead or Into a Rigid Conduit

### Specifications

Material	Zinc Die Cast
----------	---------------

### Classifications

Brand Name	T&B Liquidtight Fittings
------------	--------------------------

### Dimensions

Size	1-1/4 Inch
------	------------

### Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	None
Material housing	Zinc die-cast

by ABB