



Representative Image

Catalog No. 035-72775-6

Description: STRN REL CONN 1/2IN 0.625-0.750 STL

UPC No 786210480541

Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors

1/2 Inch Insulated Watertight Strain Relief Connector, Straight, Cable Size 0.625 to 0.750 Inch, Steel, Zinc Plated

Descriptors

Category	Liquid tight connectors
Application	Provide Means for Passing a Cord Cable, Armored or Unarmored, Into an Enclosure, Through a Bulkhead or Into a Rigid Conduit

Specifications

Material	Steel
Finish	Zinc Plated

Classifications

Brand Name	T&B Liquidtight Fittings
------------	--------------------------

Dimensions

Size	0.625 to 0.750 Inch
------	---------------------

Compliance and Certifications

TSCA	TSCA Section 6(h) Compliant
------	-----------------------------

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Thread
Thread type	NPT
Thread connection size	None
Material housing	Steel

by ABB