



Representative Image

Catalog No. 040-2521

Description: DURAPLATED CONNECTOR

UPC No 786210767758

Home > Cable Protection Systems > T&B Liquidtight Fittings > Liquid tight connectors

Zinc Strain Relief Fitting, Duraplated Connector, 1/2 Inch, Straight, for Round Flexible Cord and Power Cable, Neoprene Bushing, Range 0.250 to 0.375 Inch / 6.350 to 9.525mm Diameter, CSA Certified Submersible, UL Listed Liquidtight, 25 Pieces

Descriptors

Category	Liquid tight connectors
Special Features	Dura-Plate Finish.

Specifications

Material	Zinc Die Cast
----------	---------------

Classifications

Brand Name	T&B Liquidtight Fittings
Standard	CSA, UL

Dimensions

Size	1/2 Inch
------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 247 Compliant
TSCA	TSCA Section 6(h) Compliant