

**Catalog No. PLM2412C****Description: LOAD CTR MLO 125A 24CKT N1 GRAY PON****UPC No 783164640601****Home > Load Centers > Load Centers**

PowerMark PRO convertible plug-on neutral load centers arrive as main lug but have the capability to have a main circuit breaker installed in the field. All ABB load centers are rated up to 60 degree/75 degree centigrade and suitable for use as service entrance equipment when installed in accordance with electrical code. The PLM2412C features space for 24 - 1" circuit breakers and 48 circuits, a 125-ampere bus rating, copper bus bars, and a gray combination/flush enclosure.

Descriptors

Category	Load Centers
GO Schedule	RI
Grouping	Single Phase - USA

Specifications

# Branch Circuit 250A	24
1" Space	24
1/2" Space	0
Amperage	125 A
Circuit Breaker Style	Plug-On Neutral
Device type	Convertible
Door	Yes
Enclosure	Indoor
Enclosure Type	Indoor, Combination
Factory Installed Ground Kit	Yes
Feed	Either
Input/Output Voltage	120/240V ac
Interrupt Rating	22k
Interrupting Capacity Rating	22
Load Center Type	Plug-On Neutral Load Centers
NEMA Rating	NEMA 1
No of Circuits	48
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----

Dimensions

Depth	3.805 in
Width	14.11 in