



Representative Image

Catalog No. 9T21B1006G02

Description: 1A,10kVA,240x480-120/240,115C,3R,QMS

UPC No 783173003404

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

Specifications

Phase	1
PriVoltage	240x480
SecVoltage	120/240
KVA	10.0 KVA
Coil Material	AL
TempRise	115.0 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
Impedance	3.4 %
FrameSize	19400
Net Weight	198
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12
KFactor	K1
Enclosure Type	NEMA 3R
Net Weight	198
Sound	Std
GSA Compliance	No

Classifications

UL	Yes
cUL	Yes
CE	No

Dimensions	
Width	12.5 in
Depth	12.5 in
Height	17.1 in