

**Catalog No. PM4020R****Description: LOAD CTR MCB 200A 40CKT N3R GRAY PON****UPC No 783164640878****Home > Load Centers > Load Centers**

PowerMark PRO main breaker plug-on neutral load centers arrive with a main circuit breaker installed for a convenient and swift install. Main circuit breakers allow for the user to stop the flow of electricity in the load center, shutting off all the power in the residence. The PM4020R features spaces for 40 - 1" circuit breakers and 80 circuits, a 200-ampere bus rating, copper bus bars, and a gray NEMA 3R enclosure.

Descriptors

Category	Load Centers
GO Schedule	RI
Grouping	Single Phase - USA

Specifications

# Branch Circuit 250A	40
1" Space	40
1/2" Space	0
Amperage	200 A
Circuit Breaker Style	Plug-On Neutral
Device type	Main Breaker
Door	Yes
Enclosure	Outdoor
Enclosure Type	Outdoor, Surface
Factory Installed Ground Kit	Bonding screw included
Feed	Top
Input/Output Voltage	120/240V ac
Interrupt Rating	22k
Interrupting Capacity Rating	22
Load Center Type	Plug-On Neutral Load Centers
NEMA Rating	NEMA 3R
No of Circuits	80
Phase	1 Phase
Service & Voltage	1 Phase, 3 Wire, 120/240V ac
Wires	3 Wire

Classifications

UL/CUL Listing	UL
----------------	----

Dimensions

Depth	3.805 in
Width	14.11 in