

Alternate Catalog No. PSTX470-600-70
Catalog No. 1SFA898116R7000

Description: "PSTX470, 600V, 100-250VAC"

UPC No 7320500508954

Home > Soft Starters > Softstarter - Open (PSTX)



Representative Image

Descriptors

Category	Softstarter - Open (PSTX)
----------	---------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-600 V
Control Voltage	100-250 V
Normal Duty: Output Current (A)	480
Normal Duty: Motor Power (HP) at 208V	150
Normal Duty: Motor Power (HP) at 230V	200
Normal Duty: Motor Power (HP) at 460V	400
Normal Duty: Motor Power (HP) at 575V	500
Heavy Duty: Output Current (A)	361
Heavy Duty: Motor Power (HP) at 208V	125
Heavy Duty: Motor Power (HP) at 230V	150
Heavy Duty: Motor Power (HP) at 460V	300
Heavy Duty: Motor Power (HP) at 575V	350
Power Dissipation In Watts	99
Height (Inches)	19.4
Width (Inches)	14.2
Depth (Inches)	11.1

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Weight (lb)	55.1
Height (mm)	493
Width (mm)	361
Depth (mm)	282.1

Dimensions

Weight (kg)

25