



### Catalog No. 9T51B0089

Description: "1C,0.75kVA,600-120/240,100C,3R,60Hz,QB"

UPC No 783173008942

Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA

ABB's QB single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

### Descriptors

|             |   |
|-------------|---|
| Category    | Single-Phase: .050kVA-3kVA and 5kVA-25kVA |
| GO Schedule | T5  |

### Specifications

|                  |          |
|------------------|----------|
| Phase            | 1        |
| PriVoltage       | 600      |
| SecVoltage       | 120/240  |
| KVA              | 0.75 KVA |
| Coil Material    | CU       |
| TempRise         | 100.0 °C |
| ElecShield       | N        |
| Sub Type         | Standard |
| Frequency        | 60 Hz    |
| FrameSize        | 12200    |
| Net Weight       | 25       |
| TempClass        | 180.0 °C |
| AmbTemp          | 40.0 °C  |
| InsulSys         | IS-12    |
| EnergyEfficiency | None     |
| KFactor          | K1       |
| Enclosure Type   | NEMA 3R  |
| Net Weight       | 25       |
| Sound            | Std      |
| GSA Compliance   | Yes      |

### Classifications

|     |     |
|-----|-----|
| UL  | Yes |
| cUL | Yes |
| CE  | No  |

## Dimensions

|        |        |
|--------|--------|
| Width  | 7.9 in |
| Depth  | 5.5 in |
| Height | 9.6 in |