



Representative Image

Alternate Catalog No. SU203MR-K25
Catalog No. 2CDS273347R0517

Description: MCB SU200MR RTT 3P K 25A BCP

UPC No 4016779958516

Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs

SU203MR-K25 MCB K-Char., 10kA, 25A, 3P, RTT UL 489, Ring Cable Lug

Descriptors

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

Specifications

Number of Poles	3
Tripping Characteristic	K
Rated Current	25 A
Product Main Type	SU200MR
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Power Loss	at Rated Operating Conditions per Pole 3.2 W