



Representative Image

Catalog No. 2TLA042022R3000**Description: MAGNE 4X DYN M12-5****UPC No 7350024480955****Home > Machine Safety > Safety Sensors, Switches, Locks & Gate Boxes**

Electromagnetic lock with integrated Adam DYN for safe interlocking and M12-5 connector. Locking with +24VDC. Holding force 1500N. Protection class IP67. Eva actuator and anchor plate must be ordered separately: "Eva General code" or "Eva Unique code", "Magne Anchor 32A" or "Magne Anchor 32B".

Descriptors

Category	Safety Sensors, Switches, Locks & Gate Boxes
Type	Process Lock

Specifications

Product Class	Safety Locks & Process Locks
Product Main Type	Magne
Supply Voltage	24VDC
Outputs	DYNlink
Number of Outputs	1
Degree of Protection	IP67

Classifications

ETIM 4	EC002593 - Position switch with interlocking
ETIM 5.0	EC002593 - Position switch with interlocking
ETIM 6.0	EC001769 - Permanent magnet for door locking mechanism
ETIM 7	EC001769 - Permanent magnet for door locking mechanism
ETIM 8 (Etim8)	EC001769 - Permanent magnet for door locking mechanism

Dimensions

Product Net Depth / Length	30 mm
Product Net Height	274 mm
Product Net Width	35 mm
Product Net Weight	0.7kg

Safety Information

Performance Level	Up to e
-------------------	---------