



Representative Image

Alternate Catalog No. PSR6-600-11 Catalog No. 1SFA896104R1100

Description: PSR SSTR,600V/24V AC/DC,6.1A

UPC No 7320500477151

Home > Soft Starters > Softstarter - Open (PSR)

PSR softstarter - The compact rangeThe PSR softstarter range is a simple yet reliable starting solution that utilizes only the most basic of soft starting features: soft start and stop. It performs well in applications requiring many starts per hour and is perfect for installations where you need to save space. **Main benefits*** Small and compact starting solution* Can perform many starts per hour* Reduce energy loss at full speed with built-in bypass. **Main features*** Rated operational current: 3 to 105 A* Operational voltage: 208-600 V AC* Control supply voltage: 24 V AC/DC or 100-240 V AC.

Descriptors

Category	Softstarter - Open (PSR)
----------	--------------------------

Specifications

Product Type	Soft Starters
Input Voltage	208-600 V
Control Voltage	24Vac/dc
Normal Duty: Output Current (A)	6.1
Normal Duty: Motor Power (HP) at 460V	3
Power Dissipation In Watts	2.9
Height (Inches)	5.5
Width (Inches)	1.8
Depth (Inches)	4.5

Classifications

RoHS Indicator	Yes
UL/CUL Listing	Yes

Dimensions

Weight (lb)	0.99
Height (mm)	140
Width (mm)	45
Depth (mm)	113.5
Weight (kg)	0.45