



Representative Image

Alternate Catalog No. SU204MR-K4
Catalog No. 2CDS274347R0337

Description: MCB SU200MR RTT 4P K 4A BCP

UPC No 4016779959339

Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs

SU204MR-K4 MCB K-Char., 10kA, 4A, 4P, RTT UL 489, Ring Cable Lug

Descriptors

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

Specifications

Number of Poles	4
Tripping Characteristic	K
Rated Current	4 A
Product Main Type	SU200MR
Rated Voltage (V)	(480Y / 277 V AC) (96 V DC)
Interrupting Rating acc. to UL489	(480Y / 277 V AC) 10 kA (96 V DC) 10 kA
Power Loss	at Rated Operating Conditions per Pole 1.8 W