



Representative Image

Catalog No. 9T21C3305**Description: 1C,15kVA,480-120/240,115C,3R,60Hz,QMS****UPC No 783173011775****Home > Transformers > Dry Type, Encapsulated, Enclosed > Single-Phase: .050kVA-3kVA and 5kVA-25kVA**

ABB's QMS single phase transformers feature encapsulated core and coils in a NEMA 3R nonventilated weatherproof enclosure. Knock outs provided on back and bottom. Mounting holes on side for easy access. Wiring compartment includes ground stud.

Descriptors

Category	Single-Phase: .050kVA-3kVA and 5kVA-25kVA
GO Schedule	T7

Specifications

Phase	1
PriVoltage	480
SecVoltage	120/240
KVA	15.0 KVA
Coil Material	CU
TempRise	115.0 °C
ElecShield	N
Sub Type	Standard
Frequency	60 Hz
FrameSize	19500
TempClass	180.0 °C
AmbTemp	40.0 °C
InsulSys	IS-12

Classifications

UL	Yes
cUL	Yes