



Representative Image

## Alternate Catalog No. SU202M-K15 Catalog No. 2CDS272337R0457

**Description:** UL489 MCB 2P K 15A 480/277

**UPC No** 4016779932738

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU202M-K15 Miniature Circuit Breaker K-Char., 10kA, 15A, 2P UL489

### Descriptors

|          |                       |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

### Specifications

|                                                |                                                       |
|------------------------------------------------|-------------------------------------------------------|
| Interrupting Rating acc. to UL489              | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA            |
| Number of Poles                                | 2                                                     |
| Power Loss                                     | 4,8 W<br>at Rated Operating Conditions per Pole 2,4 W |
| Product Main Type                              | SU200M                                                |
| Rated Current                                  | 15 A                                                  |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA                                      |
| Rated Voltage (V)                              | (480Y / 277 V AC)<br>(96 V DC)                        |
| Standards                                      | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489            |
| Tripping Characteristic                        | K                                                     |