



Representative Image

**Alternate Catalog No. SU203M-K6**  
**Catalog No. 2CDS273337R0377**

**Description:** UL489 MCB 3P K 6A 480/277

**UPC No** 4016779930321

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU203M-K6 Miniature Circuit Breaker K-Char., 10kA, 6A, 3P UL489

## Descriptors

|          |                       |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

## Specifications

|                                                |                                                     |
|------------------------------------------------|-----------------------------------------------------|
| Interrupting Rating acc. to UL489              | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA          |
| Number of Poles                                | 3                                                   |
| Power Loss                                     | 6 W<br>at Rated Operating Conditions per Pole 2,0 W |
| Product Main Type                              | SU200M                                              |
| Rated Current                                  | 6 A                                                 |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA                                    |
| Rated Voltage (V)                              | (480Y / 277 V AC)<br>(96 V DC)                      |
| Standards                                      | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489          |
| Tripping Characteristic                        | K                                                   |