



Representative Image

**Alternate Catalog No. SU203M-Z25**  
**Catalog No. 2CDS273337R0518**

**Description:** UL489 MCB 3P Z 25A 480/277

**UPC No** 4016779933452

**Home > Modular DIN Rail Products > Mini Circuit breakers**

SU203M-Z25 Miniature Circuit Breaker Z-Char., 10kA, 25A, 3P UL489

## Descriptors

|          |                       |
|----------|-----------------------|
| Category | Mini Circuit breakers |
|----------|-----------------------|

## Specifications

|                                                |                                                       |
|------------------------------------------------|-------------------------------------------------------|
| Interrupting Rating acc. to UL489              | (480Y / 277 V AC) 10 kA<br>(96 V DC) 10 kA            |
| Number of Poles                                | 3                                                     |
| Power Loss                                     | 9,6 W<br>at Rated Operating Conditions per Pole 3,2 W |
| Product Main Type                              | SU200M                                                |
| Rated Current                                  | 25 A                                                  |
| Rated Ultimate Short-Circuit Breaking Capacity | (400 V AC) 15 kA                                      |
| Rated Voltage (V)                              | (480Y / 277 V AC)<br>(96 V DC)                        |
| Standards                                      | CSA 22.2 No. 5<br>IEC/EN 60947-2<br>UL 489            |
| Tripping Characteristic                        | Z                                                     |