



Representative Image

## Catalog No. 3120-30

**Description: 2 INCH AROMRED CABLE CONN**

**UPC No 786210947709**

**Home > Cable Protection Systems > T&B Cord & Cable Fittings > Flex connectors**

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 2 Inch, Knockout Size 2 Inch, Cable Range 2.312 to 2.500 Inch, Malleable Iron with Zinc Plating, Nylon Insulated

### Descriptors

Category	Flex connectors
Special Features	The Tough Lining of Insulation and The Tite-Bite Principles Make These Connectors a Must When Conductors are Subject to Conditions of Vibration or Strain.
Application	For Use with Armored Cable and Flexible Metal Conduit.

### Specifications

Conductor Range	2.312 to 2.500 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

### Classifications

Brand Name	T&B Cord & Cable Fittings
Standard	UL E23018

### Dimensions

Size	2 Inch
------	--------

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other

