



Representative Image

Catalog No. 3121-15

Description: 2-1/2 INCH AROMRED CABLE CONN

UPC No 786210947693

Home > Cable Protection Systems > T&B Cord & Cable Fittings > Flex connectors

Metal-Clad and Armored Cable Fitting, Straight, Trade Size 2-1/2 Inch, Knockout Size 2-1/2 Inch, Cable Range 2.812 to 3.062 Inch, Malleable Iron with Zinc Plating, Nylon Insulated

Descriptors

Category	Flex connectors
Special Features	The Tough Lining of Insulation and The Tite-Bite Principles Make These Connectors a Must When Conductors are Subject to Conditions of Vibration or Strain.
Application	For Use with Armored Cable and Flexible Metal Conduit.

Specifications

Conductor Range	2.812 to 3.062 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

Classifications

Brand Name	T&B Cord & Cable Fittings
Standard	UL E23018

Dimensions

Size	2 1/2 Inch
------	------------

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	2 1/2 inch
Model	Straight
Revolving thread	N



ETIM	EC001180 Screw connection for protective metallic hose
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Other