



Representative Image

Catalog No. 3137-50

Description: 1 TITE BITE 90 DEG INSUL BULK PACK

UPC No 786209994011

Home > Cable Protection Systems > T&B Cord & Cable Fittings > Flex connectors

Metal-Clad and Armored Cable Fitting, 90 Degree Bend, Trade Size 1 Inch, Knockout Size 1 Inch, Cable Range 1.250 to 1.468 Inch, Malleable Iron with Zinc Plating, Nylon Insulated

Descriptors

Category	Flex connectors
Special Features	By Far The Easiest and Best to Install When Making Sharp Bends At The Enclosure or Equipments.
Application	For Use with Armored Cable and Flexible Metal Conduit.

Specifications

Conductor Range	1.250 to 1.468 Inch
Material	Malleable Iron
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

Classifications

Brand Name	T&B Cord & Cable Fittings
Standard	UL E23018

Dimensions

Size	1 Inch
------	--------

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1 inch
Model	90°-elbow
Revolving thread	N
Construction type	External thread

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
Connection type screw connection to housing	Other
Material housing	Other

Certification/Standard

CLASS	File Number	Class	CCN	Certificate Number	Library Number
UL	E1383	N/A	N/A	N/A	N/A
UL	E23018	N/A	N/A	N/A	N/A