

Alternate Catalog No. SU201M-C50
Catalog No. 2CDS271337R0504

Description: UL489 MCB 1P C 50A 240

UPC No 4016779930949

Home > Circuit Breakers > Miniature Circuit Breakers > UL 489 Branch Circuit MCBs

SU201M-C50 Miniature Circuit Breaker C-Char., 10kA, 50A, 1P UL489



Representative Image

Descriptors

Category	UL 489 Branch Circuit MCBs
----------	----------------------------

Specifications

Number of Poles	1
Tripping Characteristic	C
Rated Current	50 A
Standards	CSA 22.2 No. 5 IEC/EN 60947-2 UL 489
Product Main Type	SU200M
Rated Voltage (V)	(240 V AC) (48 V DC)
Interrupting Rating acc. to UL489	(240 V AC) 10 kA (48 V DC) 10 kA
Rated Ultimate Short-Circuit Breaking Capacity	(230 V AC) 15 kA
Power Loss	4,5 W at Rated Operating Conditions per Pole 4,5 W