



Representative Image

Catalog No. 3302SL

Description: 3302 WITH A SLOTED SCREW

UPC No 786210946900

Home > Cable Protection Systems > T&B Cord & Cable Fittings > Flex connectors

Sheathed Cable Fitting, Straight, Knockout Size 1/2 Inch, Two Screw Connector with Slotted Screw, Steel with Zinc Plating

Descriptors

Category	Flex connectors
Special Features	Rounded Cable Grip and Smooth Bushing Protect The Cable Sheath and Wire Insulation. Since Saddle is Threaded, Screws Do Not Travel or Extend Beyond The Connector Body As It is Clamped to The Cable. An Extra Lip on The Saddle Closes The Unused Part of The Connector Opening.
Application	To Connect Non-Metallic Sheathed Cable and Flexible Cord to a Box or an Enclosure.

Specifications

Material	Steel
Finish	Electro Zinc Plated
Color	Metallic

Classifications

Brand Name	T&B Cord & Cable Fittings
Standard	UL e17583

Dimensions

Size	1/2 Inch
------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N

by ABB

ETIM	EC001180 Screw connection for protective metallic hose
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Steel