



Catalog No. 3303SL

Description: 3303 WITH SLOT HEAD SCREW

UPC No 786210933924

Home > Cable Protection Systems > T&B Cord & Cable Fittings > Flex connectors

3/4 Inch Non-Metallic Sheathed Cable - Two Screw Connector with Slotted Head Screw, For Non-Metallic Sheathed Cables 8/2, 8/3 or 6/2, For Multiple (2) NM Cables 12/2 or 14/3, For Flexible Cords Cable Opening .530 Inch to .835 Inch, For Multiple Flexible Cords (.530 Combined Diameter Minimum) (2) 18/3 Minimum, For Service Entrance Cables Minimum Opening .395 Inch X .622 Inch

Descriptors

Category	Flex connectors
Special Features	Rounded Cable Grip and Smooth Bushing Protect The Cable Sheath and Wire Insulation, Since Saddle is Threaded, Screws Do Not Travel or Extend Beyond The Connector Body As It is Clamped to The Cable, An Extra Lip on The Saddle Closes The Unused Part of The Connector Opening.

Specifications

Material	Steel
Finish	Electro Zinc Plated
Color	Metallic

Classifications

Brand Name	T&B Cord & Cable Fittings
------------	---------------------------

Dimensions

Size	3/4 Inch
------	----------

Compliance and Certifications

RoHS	RoHS3 Compliant
------	-----------------

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3/4 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Type of connection	Other
Thread connection size	Other

by ABB