



Representative Image

Catalog No. 1SNA645017R2200

Description: RB111-230VUC Interface relay R600 1n/o,A1-A2=230VAC/DC,5-250VAC/60mA-6A

UPC No 4013614507854

Home > Controls & Protective Relays > Interface Relays & Optocouplers

Descriptors

Category	Interface Relays & Optocouplers
----------	---------------------------------

Specifications

Function	Boxed interface relay R600
Rated Control Supply Voltage	230 V AC / DC
Output Signal	5 ... 250VAC / 60mA ... 6A
Terminal Type	Screw Terminals
Output	1 n/o contact
Contact material	silver-tin-oxide (AgSnO2)
Product Main Type	R600
Sub-Function	Relay with built in LED
RoHS Status	Following EU Directive 2011/65/EU
Object Classification Code	K

Classifications

ETIM 4	EC001437 - Switching relay
ETIM 5.0	EC001437 - Switching relay
ETIM 6.0	EC001437 - Switching relay
ETIM 7	EC001437 - Switching relay
eClass	7.0 27371601

Dimensions

Product Net Width	6 mm
Product Net Height	67.5 mm
Product Net Depth / Length	70 mm
Product Net Weight	0.02kg

Package Information

Package Level 1 Units	10 piece
-----------------------	----------

Package Information

Package Level 1 Width	73 mm
Package Level 1 Height	71 mm
Package Level 1 Depth / Length	80 mm
Package Level 1 Gross Weight	0.23 kg
Package Level 1 EAN	3472596450175

Ordering

Minimum Order Quantity	10
Customs Tariff Number	85364900
ECCN	N
ECN	N
ABB MDF Code	3DL - Relays (LV / Control + Protection)
ABB Business Unit	ELSP - Smart Power